



MANUAL WASHING HEAD

D SYSTEM

- Specifically designed for manual keg washing/filling applications
- Enlarged inlet and outlet ports for fast flow
- Stainless steel for durability and chemical resistance
- Handle will withstand autoclave temperatures



7485-CCLS



7485-CC

Part No.	Description	Shipping Weight
□ 7485-CC	Complete	1 kg
		2 lbs
□ 7485-CCLS	Less shutoffs	1 kg
		2 lbs

Use

- Specifically designed for manual keg washing / filling applications. Keg is inverted and wash solutions are injected under pressure through the beer outlet. This allows the caustic, sanitizer and then the rinse water to enter the keg through the keg valve and cascade down the inverted keg's inner surface. The wash solution and rinse water is then evacuated through the keg valve CO2 ports and finally out the CO2 port on the wash/fill head.
- A keg can be quickly emptied when the wash/fill head is connected to an upright keg. Or a keg can be filled using the same technique.
- Shutoffs (7419-1) are included with the 7485-CC to allow quick turn off from the inlet source and attachment to the next keg.

NOTE: If purchasing as a replacement for your existing equipment, please check with your keging equipment manufacturer for compatibility. Your wash/fill coupler may have been modified from the original Micro Matic specifications. Flow rate may be inadequate for keg cleaning in some applications.

Dimensions

